








PCB LAYOUT(Tolerance:±0.05)



PIN	DIM A	DIM B
2x2	3.00	9.65
2x3	6.00	12.65
2x4	9.00	15.65
2x5	12.00	18.65
2x6	15.00	21.65
2x7	18.00	24.65
2x8	21.00	27.65
2x9	24.00	30.65
2x10	27.00	33.65
2x11	30.00	36.65
2x12	33.00	39.65

Specifications:

Contact resistance:≤10mΩ

Insulation resistance:≥1000MΩ

Rated voltage:250V AC DC

Rated current:5.0A AC DC

Withstand Voltage: 1000V AC/minute

Temperature Range:−25 ℃~ +85℃

Housing:LCP UL94V-0,BLACK

Contacts:Brass/MATTE Sn-plated

Solder Tabs:Brass/MATTE Sn-plated

ORDER INFORMATION:

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	MX3.0-2xXXAWT	UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	MX3.0-2xXXAWT	SPECIFIED,TOLERANCE:		X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	