





R-4



Rating: 16A 125V AC (UL CUL)

16A 250V AC (UL CUL TUV CQC)



Contact Resistance: 50m Ω (Max)Insulation Resistance: DC 500V 100M Ω (Min)

Dielectric Strength: AC1500V 1 minute


Electrical life: 10,000 cycles

Operating Temperature: 0°C~85°C


Safety Approval:



CUT-OUT



	X	Y
0.75~1.25	28.0+0.10	22.0+0.10
1.25~2.00	28.2+0.10	22.0+0.10
2.00~3.00	28.4+0.10	22.0+0.10



ON-OFF

MATERIAL:

Body:Nylon66,UL rated:94V-2 min

Actuator: Pc/Nylon66,UL rated:94V-2 min

Terminal:Brass with silver-plate

				公差 TOLERANCES		.X± 0.3 .XX± 0.15		角度 ± 1°		单位 DIMENSION UNIT mm.	
				版本 VERSION	A0	比例尺 SCALE	NONE	日期 DATE	2014.07.15	品名	图 号
										TITLE	
				核准	王龙	核对	杜沛钧	绘图	巫舒淇	R-4-210-C5L-BG(220V)	R-4-210-C4L-BG(220V)_A0
版本 VER.	变更说明	CHANGE DESCRIPTION	日期 DATE	ECN NO.		APPROVED BY		CHECKED BY			