








D		E		F	
版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2021/1/15	①	1.50-K型卧式WTB胶芯带扣	PA6T UL94V-0 米白色 LCP UL94V-0 本色
			②	1.50-K型卧式WTB端子	黄铜/表面镀雾锡




CKT	DIM A	DIM B	DIM C
2	1.50	3.35	4.46
3	3.00	4.85	5.96
4	4.50	6.35	7.46
5	6.00	7.85	8.96
6	7.50	9.35	10.46
7	9.00	10.85	11.96
8	10.50	12.35	13.46
9	12.00	13.85	14.96
10	13.50	15.35	16.46
11	15.00	16.85	17.96
12	16.50	18.35	19.46
13	18.00	19.85	20.96
14	19.50	21.35	22.46
15	21.00	22.85	23.96
16	22.50	24.35	25.46

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 350V, AC/DC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A , AC/DC.
- 7 产品料号:

WT150K1W—** * *—***

NO OF CKT (产品PIN数) 流水码
Plating (电镀方式) Packing (包装方式)
0:端子全雾锡 R: TAPE & REEL 卷装
1:端子全金 (G/F)
OVERALL)
2:端子全亮锡



RoHS

ZGWD 浙江温达电子有限公司
ZHEJIANG WENDA ELECTRONICS CO., LTD.

品名 (TITLE) 1.50 Pitch K型卧式(带扣)WTB业务图		制图 (DR) ANLAN	
料号 (DWG.NO) WT150K1W-****-***		校对 (CKHD) 田峰	
		审核 (APPD) 黄志明	
比例 (SCALE) E		单位 (UNITS) mm	张数 (SHEET) 1 OF 1
			SIZE A4
			REV A
F			