








MR-4



Rating: 10A 125V AC (UL CUL) 
6A 250V AC (UL CUL TUV CB) 
Contact Resistance: 50mΩ Max
Insulation Resistance: DC 500V 100MΩ Min
Dielectric Strength: AC1500V 1 minute
Electrical life: 10,000 cycles
Operating Temperature: 0°C~85°C



CUT-OUT


	X	Y
0.75~1.25	19.2-0.1	21.8~21.9
1.25~2.00	19.4-0.1	21.8~21.9
2.00~3.00	19.8-0.1	21.8~21.9

MATERIAL:

Body:Nylon66, UL rated:94V-2 min

Actuator:PC

Terminal:Brass,silver or tin plated



Marking	0	1	2	3	4	5	7	8	9
None									
	ON	OFF	ON	OFF	ON	OFF	ON	OFF	ON

公差	版本	比例尺	角度	单位	图号
TOLERANCES	VERSION	SCALE	ANGLE± 1°	DIMENSION UNIT	DRAWING NO
.X± 0.3 .XX± 0.15	A1	NONE	DATE	MR-4-210-C5L-BG	MR-4-210-C5L-BG_A1
2020.06.28	N/A	核 对	2020.06.28		
变更说明	重新整理后发行	核 准			
CHANGE DESCRIPTION	变更后说明	APPROVED BY			
版本 VER.					