


NOTES:
1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.
CONTACT: COPPER ALLOYS.
2.PLATING:
UNDERPLATE: NICKEL 50u"
CONTACT AREA: 80u" TIN OVER NICKEL.
3.MULTIMEDIA CARD COMPATIBLE

尺寸表			
PIN	DIM A	DIM B	DIM C
6	2.5	3.6	8.6
8	3.5	4.6	9.6
10	4.5	5.6	10.6
12	5.5	6.6	11.6
14	6.5	7.6	12.6
16	7.5	8.6	13.6
18	8.5	9.6	14.6
20	9.5	10.6	15.6
22	10.5	11.6	16.6
24	11.5	12.6	17.6
26	12.5	13.6	18.6
28	13.5	14.6	19.6
30	14.5	15.6	20.6
32	15.5	16.6	21.6
34	16.5	17.6	22.6
36	17.5	18.6	23.6
38	18.5	19.6	24.6
40	19.5	20.6	25.6
42	20.5	21.6	26.6
44	21.5	22.6	27.6



05C20XXPZ

Z:positive F:negative

P=0.5mm

H=2.0mm

PIN=06-44

P:Tin G:Gold

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	05C20XXPZ	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	05C20XXPZ			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
							ANGULAR	±3°	
							FILE.NO.		