






TYPE-1

TYPE-2



TYPE-3

TYPE-4



MATERIALS AND FINISH
SHELL : STEEL MATERIAL, NICKEL FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR
CONTACT MATERIAL: BRASS
CONTACT FINISH : FULL GOLD FLASHED
GROUNDING BRACKET : BRASS MATERIAL, TIN FINISHED
ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C ~ +105°C

PARTS DIMENSIO			
N TABLE			
parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.0	4#40
3	4.8	11.8	M3
4	5.8	11.8	M3
5	4.8	11.8	M2.6
6	5.8	12.0	M2.6
7	6.0	12.0	4#40

DMRH-XXPM-XX

TYPE

PIN

F:Female M:Male

Color:W:white B:black BL:blue

No. of Contact	A	B	C	E
15	30.90	24.99	16.95	2.29
26	39.24	33.32	25.38	2.29
44	53.10	47.04	38.86	2.29
62	69.50	63.60	55.37	2.41

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	DMRH-XXPM-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	DMRH-XXPM-XX			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				FILE.NO.	