





REV.	ECN. NO.	APPD.



CIRCUIT DIAGRAM

P.C.B LAND DIMENSION



Specification

Maximum Voltage	16VDC
Maximum Current DC	50mA
Dielectric Strength	250 VA C(1mn)
Contact Resistance	≤500mΩ
Insulation Resistance	≥100MΩ
Operating Temperature	-35C° to 80C°
Storage Temperature	-35° C to 80° C
Bounce Time	≤10 ms

Travel:
For 160&260 gf 0.15mm ±0.1mm
For 400&600 gf 0.20mm ±0.1mm

Packaging:
Switches in reels of 3,000 pieces.
Dimensions of reels according to EIA 481B
External diameter 330mm

Mechanical

	Operating force gf	Operating force Life
YTS815 SJM	160±50	200, 000
YTS815 SJK	260±50	100, 000
YTS815 SJG	400±50	100, 000

X. ±0.50	X. ° ± 2°	UNITS mm	 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD
.X ±0.30	.X° ± 1°		
.XX ±0.10	.XX° ± 0.5°	MAT'L	PART NO. YTS 815
.XXX ± 0.05			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH	APPD: ROGER
		Q' TY	CHKD: ROC
			DR: BILLY WANG 2020/08/21
		TITLE: TACTILE SWITCH	
		DWG NO. : YTS 815	
		 	
		SCALE	SHEET
		1/1	1/1
		REV.	A1