




客户确认	
日期	



Symbol 标号	Item 项目	Specification 规格
N	No. of Conductors (导体芯数)	20
P	Pitch (间距)	1.0±0.05
TP	Total Pitch (总间距)	19.0±0.10
W	Width (总宽度)	21.0±0.10
M	Margin (边缘宽度)	1.0±0.10
L	Total Length (总长度)	100±3
T	Insertion Thickness (插入厚度)	0.30±0.05
ST	Surface Thickness (线身厚度)	0.12±0.05
SI/S2	Conductor Strip Length (裸铜长度)	4/4±1.0
B1/B2	Supporting tape Length (补强板长度)	8/8±2.0
A1	Slanting (线口倾斜度)	<0.5

ELECTRICAL CHARACTERISTICS

Conductor Resistance: JISC-3102(at20℃) 2.20Ω/KM Max.
Insulation Resistance: Apply the voltage of DC 500V
for one min 100MΩ Min.
Dielectric Strength: Apply AC 500V for one minute.
Continuity Test: Apply microtest machine No Open/Short
Rated voltage & temperature:UL Sub. 758VW-1

Material

Insulation: Flame Retardant Polyeste
Color: White
Conductor: Copper with 1u m min. tin-Plating
Supporting Tape: Flame Retardant Polyester
Color: Blue

核准:	日期:	深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD										
业务:	日期:	品名规格: FFC1.0-20P L=100mm 4/4-8/8 异面										
制图:	日期:	客户料号	C3025480	单位	mm	比例	/	图例	图纸编号	F-FFC1Z20P-1000	版本	A
LYF	2022-06-10											