






NOTES:
 INSULATION RESESTANCE(MIN.):1000MOHMS
 CURRENT RATING(MAX.): 3amp AC/DC
 WITHSTANDING VOLTAGE:1000VAC
 CONTACT RESISTANCE(MAX.)30m chms
 OPERATION TEMPERATURE:-55°~+105°
 MATERIAL:
 CONTACT: PHOSPHOR BRONZE
 INSULATION: PBT+30%GLASS FIBER.UL 94V-0
 SHELL:STEEL
 NOTICE: THE DIMENSION MAKED WITH " * " MUST BE CONTROLLED BY QC.

PARTS DIMENSION TABLE			
	a	b	
	inner thread		UNC 4#40
parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.0	4#40
3	4.8	11.8	M3
4	5.8	11.8	M3
5	4.8	11.8	M2.6
6	5.8	12.0	M2.6
7	6.0	12.0	4#40



DP-XXPF-XX

TYPE

PIN

F:Female M:Male

Color:W:white B:black BL:blue

POS.	A	B	C	D	E	G
9	30.80	24.99	16.34	19.00	15.60	4.0/4.6
15	39.20	33.32	24.76	27.70	24.60	4.0/4.6
25	53.05	47.04	38.33	41.10	38.10	4.0/4.6
37	69.50	63.50	54.89	57.30	54.30	4.0/4.6

_____		new		2015/5/3		A	瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	DP-XXPF-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25		
			MODEL NAME	DP-XXPF-XX		X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15
				FILE.NO.				