








PCB LAYOUT/TOP VIEW

TOLERANCE=± 0.05

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	TITLE:
CHECKED:	DATE:	RJ11-4P/4C SMT 立贴 (RJ11-SMT-52E-4P4C)
DRAWN:	DATE:	PART. NO.
L. YUN	2018-05-14	R-RJ11M04P-A000

深圳市灿科盟实业有限公司
CKMTW CHANKLEMENT INDUSTRY CO., LTD

UNIT	mm	SCALE	free	REV.	A	HY04
FILE NO.	CKMTW-RJ11-0069	REV.	A	HY04		

- NOTES:
1. 端子: C5191-H T=0.35 ± 0.01. 电镀半金锡镀金3U"
 2. 卡勾: C2680-EH T=0.40 ± 0.01. 电镀镍底50-80u", 亮锡100-120u"
 3. 塑胶: LCP 黑色UL94-V0
 4. 弹片750次插拔测试不下陷
 5. 产品符合RoHS环保要求