





NOTES:

ELECTRICAL:



- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :15 AMP.
- 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :1000 MEGOHMS MIN @ 500V DC .
- 5.DIELECTRIC STRENGTH :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE Ø0.46mm ROUND PIN.
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.OPERATING :750 CYCLES MIN.
- 5.Shielding: 0.20mm Thickness Steel Strip Plated With Nickel.
- 6.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.Temperature Range : -25℃~+85℃
- 2.Relative Humidity : 90~95% (40±2℃)



PCB LAYOUT

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	TITLE: RJ11-6P/6C 55A 弯插 带屏蔽 灰色			
SXA	2018-01-13	PART. NO.	R-RJ11R06P-B802	UNIT	mm
		SCALE	free	REV.	A
		FILE NO.	Ckmtw-RJ11-0048	HY04	