





ASSEMBLY DIAGRAM



RECOMMENDED P.C.B BOARD LAYOUT ±0.05

NO.	PART NAME	MATERIALS	DESCRIPTION	REMARK	QTY.
1	HOUSING	NYLON UL94-V0	—	NATURAL/BLACK	1
2	CONTACT PIN	PHOSPHOR BRONZE	G/F,TIN-PLATED	—	N
3	CONTACT PIN	PHOSPHOR BRONZE	G/F,TIN-PLATED	—	N
4	SOLDER TAB	BRASS	TIN-PLATED	—	2

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS2.0.
2. PRODUCT PERFORMANCE:

- 2.1 RATED VOLTAGE(MAX.):50V AC/DC
 - 2.2 RATED CURRENT(MAX.):1A AC/DC(AWG.#28)
 - 2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
 - 2.4 INSULATION RESISTANCE:100 MΩ MIN.
 - 2.5 CONTACT RESISTANCE:30 mΩ MAX.
 - 2.6 OPERATING TEMPERATURE:-25°C to +85°C
- 3.PART NO. LEGEND:1WF02-325XXX-0000X






PIN CODE
FOR EXAMPLE, 012:12PIN

CODE(BLACK)	CODE(NATURAL)	POLES	DIM A	DIM B
—	00002	2*3P	2.00	6.00
—	00002	2*4P	3.00	7.00
00003	00002	2*5P	4.00	8.00
00003	00002	2*6P	5.00	9.00
—	00002	2*7P	6.00	10.00
00003	00002	2*8P	7.00	11.00
—	00002	2*10P	9.00	13.00
—	00002	2*11P	10.00	14.00
—	00002	2*12P	11.00	15.00
—	00002	2*13P	12.00	16.00
—	—	2*15P	14.00	18.00
—	—	2*20P	19.00	23.00
—	—	2*25P	24.00	28.00


5.0	23.10.10	Newly added product specifications	ZQH	DRAWING: LWJ	GENERAL TOLERANCE .X:=±0.30 .X°:=±2° .XX:=±0.20 .XX°:=±1° .XXX:=±0.10 .XXX°:=±0.5°	
4.0	22.10.12	Newly added product specifications	ZQH		CHECKED: Tianhai	UNIT: MM
3.0	22.06.24	Update the drawing frame	ZQH	APPROVAL: Joey		SCALE: 1/1
2.0	21.10.29	New specification number	ZQH		SHEET: 1/1	
1.0	21.03.23	NEW	LWJ			
REV.	DATE	DESCRIPTION	DRAWING			

CHIN-BAN
Electronic Technology

DESCRIPTION: PITCH1.0mm DISCONNECTABLE CRIMP STYLE CONNECFORS		
PART NO:	1WF02-325XXX-0000X	REV: 5.0
DRAWING NO:	UK0479	SIZE: A4



- NOTE:(说明)
1. PEELING OFF FORCE OF COVER TAPE: 0.6-1.0N (盖带剥离力: 0.6-1.0N) (PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.) (剥离方向如下图所示) THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT (这一要求应在装运时适用) PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION. (运输过程中不允许剥落。)




2. MATERIAL: (材料)
- CARRIER TAPE: POLYSTYREN(PS)(载带: PS)
- COVER TAPE: TAPE (盖带: TPE)
- REEL TAPE: PS(卷盘 PS)
3. PART NUMBER: (料号)
- 1WF02-325XXX-0000X

2: 自然色 3: 黑色

PACKING INFORMATION: (包装信息)

CODE(黑色)	CODE(自然色)	PIN	W	PCS/REEL	REEL/CARTON	TOTAL	CARTON
	00002	2X3	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
	00002	2X4	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
00003	00002	2X5	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
00003	00002	2X6	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
	00002	2X7	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
00003	00002	2X8	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
	00002	2X10	24.0	1000PCS	9PCS	9000PCS	350*350*296mm
	00002	2X11	32.0	1000PCS	7PCS	7000PCS	350*350*296mm
	00002	2X12	32.0	1000PCS	7PCS	7000PCS	350*350*296mm
	00002	2X13	32.0	1000PCS	7PCS	7000PCS	350*350*296mm



5.0	23.10.10	增加22/24/26PIN规格	ZengQiuHong
4.0	22.10.17	1. 增加2*3PIN/2*7PIN规格 2. 修订包装方式 3. 增加E1376专用包装图	ZengQiuHong
3.0	22.07.20	1. 增加2*5PIN规格 2. 更新图框	ZQH
2.0	21.10.30	新增PIN数	ZQH
1.0	21.06.23	NEW	LWJ
NO.	DATE	DESCRIPTION	DRAWING

DRAWING:	LWJ	GENERAL TOLERANCE
CHECKED:	Tianhai	.X: =±0.50 .X*: =±2° .XX: =±0.30 .XX*: =±1° .XXX: =±0.20 .XXX*: =±0.5°
APPROVAL:	Joey	UNIT: MM PROJECTION:
		SCALE: 1:1
		SHEET: 1/2

DESCRIPTION:	
1.00mm Wafer 双排 卧式 带扣 系列 包装图	
PART NO:	F-1WF02-325XXX-0000X
DRAWING NO:	UT0247
REV:	5.0
SIZE:	A4

CHIN-BAN
Electronic Technology