




RoHS Compliant



SEC A-A 1:1比例

Contact Number	Signal Name
1	VBUS
2	D-
3	D+
4	GND








一、Materials and electroplating specifications:

- 1.shell: SPCC; Plating nickel 80 u";
- 2.terminal:Brass; Plating nickel 30 u"
Solder foot tin plated 80U"
Gold-plated 0.5U in contact area.

3. Insulator:polybutylece terephthalate; Color:White .

二、SPECIALITY:

- 1.CONTACT RESISTANCE: 100mΩ Max;
- 2.DIELECTRIC STRENGTH: 500V/AC 1min No Breakdown
- 3.INSULATION RESISTANCE:1000MΩ Min. 500V DC
- 4.INSERTION FORCE:35N maximum
Extraction Force:10N minimum



P.C.B LAYOUT bottom view

LCK-U20	001	AH	JB-	B	G1
联晟欣 LCK	产品类别 U20:USB2.0 U30:USB3.0	产品流水料号识别码	外壳材质 AH: 铁盖 AC: 铜盖	卷边/直边 JB: 卷边 ZB: 直边	电镀规格 G1: 1U G3: 3U (以此类推)
				包装方式 L: 圆盘 B: 吸塑盒 T: 管装	

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)						联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd					
UNLESS OTHERWISE SPECIFIED,TOLERANCE:						DESIGN	Andy	DATE	2014.12.24	TITLE: USB 2.0 AF 90°插件式小脚距 白胶芯	
X. ±0.25						CHECKED		DATE			
X.x ±0.20						APPROVED		DATE			
X.xx ±0.15						PART NO: LCK-U20001-AHJB-BG1				REV: 04	SCALE: 1:1
ANGULAR ±3°						DRAWING NO:1020221305				UNIT: mm	
										SHEET: 1/1	