



NOTES:

- 1.ELECTRIC CHARACTERISTICS:
 - 1-1.CONTACT CURRENT RATING: 1.5A.
 - 1-2.CONTACT VOLTAGE RATING: 125V AC.
 - 1-3.CONTACT RESISTANCE: 50mΩ MAX.;
 - 1-4.DIELECTRIC WITHSTANDING VOLTAGE: 500V AC;
 - 1-5.INSULATION RESISTANCE: 100MΩ MIN.AT DC 500V.
- 2.MECHANICAL CHARACTERISTICS:
 - 2-1.DURABILITY:750 CYCLES.
 - 2-2.INSERTION AND EXTRACTION FORCE:
 - 2-2.1.INSERTION FORCE: 2.27Kg_f MAX.
- 3.ENVIRONMENT CHARACTERISTICS:
 - 3-1.OPERATING TEMPERATURE: -25℃ ~ +85℃.
 - 3-2.HUMIDITY:45~85% RH.



A-A VIEW

UNLESS OTHERWISE SPECIFIED TOLERANCES	SCALE:2:1	SIZE: A4	VIEW: 	MODEL TYPE:	
	UNIT: mm	REV.: A/0	OBJECT:	MINI RJ11 JACK	
DECIMALS: ANGLES:	DSND	戴龙平	DATE	2020.06.03	PART NO: RJ11-804-6P2C
X :±0.30 X :±1° X.X :±0.20 X.X :±0.5° X.XX :±0.10 X.XXX :±0.05	CHKD	王振钊	DATE	2020.06.03	
	APVD	王 丰	DATE	2020.06.05	DWN NO.:

2	HOUSING		1	PBT4830 UL-94V0	Yellow
1	TERMINAL		2	C5100 Ø0.46	Au-Plated
NO.	PART NAME	TER'NO.	Q'TY	MATERIAL	PLATING & COLOR

WENZHOU FUGANG ELECTRONICS CO., LTD.