

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW	WH.LU	23.02.03

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 8A
- 2.Withstanding voltage : AC1500V/1Min.
- 3.Wire range : 28~16AWG
- 4.Torque value : M2.5 , 3.54Lb.in

IEC Standard

1. Pollution degree	3
Overvoltage category	II
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	250V
Rate current(A)	12A

2.Wire range : 0.2~1.5mm²


3.Torque value : M2.5 , 0.4N·m

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.81mm, Poles : N=02~24P
- 3.Stripping length : 9mm
- 4.Operating temperature:-40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						
TO	Over	Over	TO	Over	Over	Over	Over	0.1/10
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150	150	≤
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'

6.RoHS Compliance



Ordering Information




JL15EDGKDM - 381 XX X XX

Pitch
381=3.81PH

No.of pins
2P~24P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Stream code
01-99



DRAW	WH.LU	SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
		UNIT	mm		
CHECK	W.CHEN	SIZE	A4	PART NO.	JL15EDGKDM-381XXXXX
APPROVE	J.CHEN	SHEET	1/1	TITLE:	JL15EDGKDM-3.81-XXP插拔式母座/带耳
		PROJ.			