







PC Board Layout
Component Side Shown

NOTES:
MATERIAL:

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi=0.46\text{mm}$.
3. PLATING : GOLD PLATING $3\mu\sim 5\mu$ OVER NICKEL

ELECTRICAL:


1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC WITHSTANDING RESISTANCE

MECHANICAL:
: 1000V AC RMS 50Hz. 1MIN.

1. DURRABILITY : 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO 85°C .
2. OPERATION : -25°C TO 85°C .



TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C km tw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	TITLE:			
HCV	2014-05-26	RJ11-6P/6C 52A 直插 全塑 无耳 黑色			
PART. NO.		R-RJ11S06P-A006			
UNIT	mm	SCALE	free		
FILE NO.	Ckmtw-RJ11-0085	REV.	A	HY04	