





NOTES:

MATERIAL :

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$
- 3.PLATING :GOLD PLATING OVER NICKEL

ELECTRICAL:



- 1.VOLTAGE RATING :125 VAC RMS,
- 2.CURRENT RATING :15 AMP.
- 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.DURABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1 STORAGE : -40 $^{\circ}$ ~-+85 $^{\circ}$
- 2. OPERATION : -25 $^{\circ}$ ~-+85 $^{\circ}$



PC Board Layout

Component Side Shown

APPROVED:		DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:		DATE:	TITLE:			
DRAWN:		DATE:	RJJ1-6P/4C 55A 弯插 全塑 无耳 黑色			
HCY		2014-05-07	PART. NO.	R-RJJ1R04P-A003		
TOLERANCE TABLE		UNIT	mm	SCALE	free	HY04
.0		±0.30				
.00		±0.20				
.000		±0.05				