







PC Board Layout

- 说明:
1. 材质:
胶芯:PBT, UL94V-0; COLOR: BLACK
端子: C5191
外壳: C2680
 2. 电镀说明:
端子: 磷铜, 先镀镍再镀金, 厚度FU
外壳: 表面镀镍
 3. 性能说明:
1) 电压: 150V AC RMS.
2) 额定电流: 1.5A.
3) 接触电阻: 40mΩ Max.
4) 绝缘电阻: 500MΩ MIN.
5) 绝缘耐压: 1000V AC.
6) 工作温度: -25° C TO +80° C.
7) 耐久性: 500 Mating Cycles MIN.

APPROVED:	DATE:	C km tw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/6C 55A-1*4 弯插 全塑 带耳 黑色			
DRAWN:	DATE:	PART. NO.	R-RJ11R06P-4001		
HCV	2014-02-11	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ11-0077	REV.	A
					HY04
TOLERANCE TABLE					
	±0.30				
	±0.20				
	±0.05				