

版次	变更摘要	日期	序号	品名	材质
0	新产品发行	2018/09/16	①	PHD2.0直针WTB胶芯	PA66 UL94V-0 米色 蓝色 橙色
1	料号更新	2024/12/13	②	PHD2.0直针WTB端子	铜合金/表面镀锡&镀金

1

1

2

2

3




3

4

4

5


5



CKT	A	B
2*2	2.0	6.0
2*3	4.0	8.0
2*4	6.0	10.0
2*5	8.0	12.0
2*6	10.0	14.0
2*7	12.0	16.0
2*8	14.0	18.0
2*9	16.0	20.0
2*10	18.0	22.0
2*11	20.0	24.0
2*12	22.0	26.0
2*13	24.0	28.0
2*14	26.0	30.0
2*15	28.0	32.0
2*16	30.0	34.0
2*18	34.0	38.0
2*20	38.0	42.0

技术指标 (Technical Index):

- 工作温度 (Temperature range): -25° C~+85° C.
- 额定电压 (Rated voltage): 250V DC/AC(rms).
- 额定电流 (Rated current): 3.0A AC,DC.
- 接触电阻 (Contact resistance): ≤20mΩ.
- 耐压值 (Dielectricwithstanding voltage): 800V AC/minute.
- 绝缘电阻 (Insulation resistance): ≥1000MΩ.
- 产品料号 (Product material No.):



WB200D1V-**-**-*--***
NO OF CKT (产品PIN数) *

Plating (电镀方式) * Packing (包装方式)
1:端子全金 (G/F OVERALL) P:BAGGING袋装
3:端子全亮锡



ZGWD 浙江温达电子有限公司 ZHEJIANG WENDA ELECTRONICS CO.,LTD			
品名 (TITLE) PHD2.0 双排直插WTB		制图 (DR) Anlan	
料号 (DWG.NO) WB200D1V-****-****		校对 (CHKD) 田峰	
比例 (SCALE) 1:1		审核 (APPD) 黄志明	
单位 (UNITS) mm		张数 (SHEET) 1 OF 1	SIZE A4
			REV A