

NOTES1:

UL Standard

- Rated voltage/current : 150V / 8A
- Withstanding voltage : AC1250V/1Min.

IEC Standard

1. Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	2.5KV
Rate voltage(V)	320V
Rate current(A)	10A

NOTES2:






- Dimension shall be interpreted per ASME Y14.5-2009
- Pitch : 3.5mm, Poles : N=04~48P(Total)
- Operating temperature: -40°C~+105°C
- Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm							0.1/10
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°	

5.RoHS Compliance

Ordering Information

JL15EDGRHBM - 350		XX	X	XX
Pitch 350=3.5PH		No.of pins 2*2P~2*24P 04=2*2P 06=2*3P 08=2*4P ...	Housing Color B=Black (Convention) G=Green U=Blue R=Red W=White Y=Yellow O=Orange E=Grey	Serial code 01-99



Recommended P.C.B Layout

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		21.12.15

DRAW	SP.ZHENG	SCALE	FIT	JILN [®] 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONICS CO.,LTD	
		UNIT	mm		
		SHEET	1/1	PART NO.	JL15EDGRHBM-350XXXXX
		PROJ.	◆	TITLE:	JL15EDGRHBM-THR-3.5-2*XXP插拔式公座/ 带耳/弯针
CHECK	W.CHEN	SIZE	A4		
APPROVE	J.CHEN	PROJ.	◆		

3	Nut	SPCC	Zn Plated
2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66+GF	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES