

NOTES1:

UL Standard

- 1.Rated voltage/current : 150V / 8A
- 2.Withstanding voltage : AC1600V/1Min.
- 3.Wire range : 28~16AWG

IEC Standard

1. Pollution degree	2	2	3
Overvoltage category	II	III	III
Rate impulse voltage(KV)	2.5KV	2.5KV	2.5KV
Rate voltage(V)	320V	160V	160V
Rate current(A)	10A		

- 2.Wire range : 0.2~1.5mm²

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.5mm, Poles : N=04~48P
- 3.Stripping length : 8~9mm
- 4.Operating temperature: -40℃~+105℃
- 5.Undimensioned tolerances:

Pitch range in mm			Nominal dimension range in mm						—	∩	∇
TO	Over	Over	TO	Over	Over	Over	Over		0.1/10		
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150	150		∠		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30		±2°		

6.RoHS Compliance

Ordering Information






JL15EDGKDH - 350 XX X XX

Pitch
350=3.5PH

No.of pins
Per row
2~24

Housing Color
B=Black
(Convention)
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Serial code



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A		NEW		22.12.15

DRAW	SHUANGPING ZHENG	SCALE	FIT	JILN [®] 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO., LTD	
CHECK	LICHAO LIU	UNIT	mm		
APPROVE	YONGLIANG GAO	SIZE	A4	PART NO.	JL15EDGKDH-350XXXXX
		SHEET	1/1	TITLE:	JL15EDGKDH-3.5-2xNP插拔式母座
		PROJ.	⌀		