





NOTES:

MATERIAL :

- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0
- 2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$
- 3. PLATING : GOLD PLATING OVER NICKEL

ELECTRICAL:


- 1. VOLTAGE RATING : 125 VAC RMS
- 2. CURRENT RATING : 15 AMP
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC
- 5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz 1MIN

MECHANICAL:

- 1. DURABILITY : 750 CYCLES MIN
- 2. PCB RETENTION PRE-SOLDER : 1 LB MIN

ENVIRONMENTAL:

- 1. STORAGE : -40 $^{\circ}$ ~+85 $^{\circ}$ C
- 2. OPERATION : -25 $^{\circ}$ ~+85 $^{\circ}$ C



PC Board Layout

Component Side Shown

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/2C 55A 弯插 全塑 无耳 黑色			
DRAWN:	DATE:	PART. NO.	R-RJ11R02P-A002	UNIT	mm
HCV	2014-05-07	FILE NO.	Ckmtw-RJ11-0080	SCALE	free
		REV.	A		HY04