

A





B

C

D

E

F



一般公差 (TOLERANCE)  
X. ±.50 .XX ±.10  
X. ±.20 .XXX ±.05  
ANGLES ±1°

版次	变更摘要	日期
0	新产品发行	2020/08/10
1	增加卡扣强度, 卡扣处增加R0.4的R角	2020/12/19
2	增加2*2/2*3规格侧面图示	2025/07/16

### 技术指标:

1. 温度范围: -25° C ~ +85° C.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: ≤ 20mΩ .
5. 绝缘电阻: ≥ 1000MΩ .
6. 额定电流: 3A AC, DC.
7. 产品料号: WB200C10-\*\* H \* \*- \*\*

NO OF CKT(产品PIN数)  流水号  
Material(胶芯材料)  Color(胶芯颜色)  
A:PA66 (低温料) 3:白色  
4:米白色  
8:绿色

CKT	A	B	C
2*2	2.00	4.5	5.9
2*3	4.00	6.5	7.9
2*4	6.00	8.5	9.9
2*5	8.00	10.5	11.9
2*6	10.00	12.5	13.9
2*7	12.00	14.5	15.9
2*8	14.00	16.5	17.9
2*9	16.00	18.5	19.9
2*10	18.00	20.5	21.9
2*11	20.00	22.5	23.9
2*12	22.00	24.5	25.9
2*13	24.00	26.5	27.9
2*14	26.00	28.5	29.9
2*15	28.00	30.5	31.9
2*16	30.00	32.5	33.9

**ZGWD** 浙江温达电子有限公司  
ZHEJIANG WENDA ELECTRONICS CO., LTD

品名 (TITLE)	制图 (DR)	ANLAN
校对 (CHKD)	田峰	
料号 (DWG.NO)	审核 (APPD)	黄志明
WB200C10-**H**-**		
比例 (SCALE)	张数 (SHEET)	SIZE REV
mm	1 OF 1	A4 A