


PC Board Layout

Component Side Shown

NOTES:

MATERIAL :

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE φ0.46mm.
- 3.PLATING :GOLD PLATING OVER NICKEL.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :15 AMP.
- 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.ELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. MIN.

MECHANICAL:

- 1.DURABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40℃~+85℃
- 2. OPERATION : -25℃~+85℃

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C kmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ11-6P/6C 55A 弯插 全塑 带耳 黑色			
DRAWN:	DATE:	PART. NO.	R-RJ11R06P-A010	UNIT	mm
HCY	2014-08-07	FILE NO.	Ckmtw-RJ11-0079	SCALE	free
			REV.	A	HY04