





NOTES:

MATERIAL :

- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0
- 2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$
- 3. PLATING : GOLD PLATING OVER NICKEL

ELECTRICAL:


- 1. VOLTAGE RATING : 125 VAC RMS
- 2. CURRENT RATING : 15 AMP
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC
- 5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz 1MIN

MECHANICAL:

- 1. DURABILITY : 750 CYCLES MIN
- 2. PCB RETENTION PRE-SOLDER : 1 LB MIN

ENVIRONMENTAL:

- 1. STORAGE : -40°C~+85°C
- 2. OPERATION : -25°C~+85°C



PC Board Layout

Component Side Shown

APPROVED:		DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:		DATE:	TITLE: RJ11-6P/6C 55A 弯插 全塑 无耳 黑色			
DRAWN:		DATE:	PART. NO. R-RJ11R06P-A004			
HCY		2014-05-07	UNIT mm	SCALE free	REV. A	HY04
TOLERANCE TABLE			FILE NO. Ckmtw-RJ11-0080			
.0		±0.30				
.00		±0.20				
.000		±0.05				