






版次	变更摘要	日期
0	新产品发行	2018/09/16
1	料号更新	2024/12/13


序号	品名	材质
①	PHDC2.0直针WTB胶芯	PA66 UL94V-0 米色
②	PHD2.0直针WTB端子	铜合金/表面镀锡



CKT	A	B
2*2	2.0	6.0
2*3	4.0	8.0
2*4	6.0	10.0
2*5	8.0	12.0
2*6	10.0	14.0
2*7	12.0	16.0
2*8	14.0	18.0
2*9	16.0	20.0
2*10	18.0	22.0
2*11	20.0	24.0
2*12	22.0	26.0
2*13	24.0	28.0
2*14	26.0	30.0
2*15	28.0	32.0
2*16	30.0	34.0
2*17	32.0	36.0
2*18	34.0	38.0
2*19	36.0	40.0
2*20	38.0	42.0

技术指标(Technical Index):

- 工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 额定电压(Rated voltage): 250V DC/AC(rms).
- 额定电流(Rated current): 3.0A AC, DC.
- 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 耐压值(Dielectricwithstanding voltage): 800V AC/minute.
- 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 产品料号(Product material No.):



WB200C1V-*** * *-*** 流水码
NO OF CKT(产品PIN数)
Plating(电镀方式) 3:端子全亮锡
(Terminal all bright tin)
Packing(包装方式) P:BAGGING袋装



一般公差(TOLERANCE)
X. ± 0.50 .XX ± 0.10
X. ± 0.20 .XXX ± 0.05
ANGLES $\pm 1^{\circ}$

ZGWD 浙江温达电子有限公司 ZHEJIANG WENDA ELECTRONICS CO.,LTD	
品名 (TITLE)	PHDC2.0 双排直插WTB
料号 (DWG.NO)	WB200C1V-***-***
比例 (SCALE)	1:1
单位 (UNITS)	mm
制图 (DR)	Anlan
校对 (CHKD)	田峰
审核 (APPD)	黄志明
张数 (SHEET)	1 OF 1
SIZE	A4
REV	A