






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.


REV.	ECN. NO.	APPD.



F
E
D
C
B
A



CIRCUIT DIAGRAM



PCB. WELDING DRAWING

Specification

Packaging:
Reel of 3,000 pieces.

Operating Life	≥300,000
Contact rating	50mA@12V DC.
Insulation resistance	≥100MΩ min.
Contact resistance	100mΩ max. initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.15±0.1mm

F	button	LCP	1	Black
E	Cover	Stainless steel	1	Gold plated
D	Dust-proof membrane	polyimide	1	orange
C	shrapnel	Stainless steel	2	Plated Ag
B	naumenon	LCP	1	Black
A	Card	Phosphor copper	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

PN	Operating Force(gf)	Height mm
YTSA034A0262501B	260±50	2.6
YTSA034A0261601B	160±50	2.6

Mechanical

X. ±0.50	X.* ± 2°	UNITS
.X ±0.30	.X* ± 1°	mm
.XX ±0.10	.XX* ± 0.5°	MAT'L
.XXX ± 0.05		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD. Email at info@yiyuanswitches.com		
FINISH		
Q'TY		

UNITS	mm
MAT'L	
FINISH	
Q'TY	

深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD	
PART NO. YTSA034	TITLE: TACTILE SWITCH 2.2x4.5mm
APPD: ROGER	DWG NO.: YTSA034
CHKD: ROC	
DR: BILLY WANG 2020/08/21	
SCALE	SHEET
1/1	1/1
REV.	A1