





NOTES:

ELECTRICAL:



- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :15 AMP.
- 3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :1000 MEGOHMS MIN @ 500V DC .
- 5.DIELECTRIC STRENGTH :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER UL94V-0.
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE Ø0.46mm ROUND PIN.
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.OPERATING :750 CYCLES MIN.
- 5.Shielding: 0.20mm Thickness Steel Strip Plated With Nickel.
- 6.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.Temperature Range : -25℃~+85℃
- 2.Relative Humidity : 90~95% (40±2℃)



PCB LAYOUT

APPROVED:		DATE:		Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:		DATE:		TITLE: RJ11-6P/4C 55A 弯插 带屏蔽 黑色					
DRAWN:		DATE:		PART. NO. R-RJ11R06P-B001					
SXA		2018-01-13		UNIT	mm	SCALE	free		
TOLERANCE TABLE									
.0		±0.30							
.00		±0.20							
.000		±0.05		FILE NO. Ckmtw-RJ11-0048 REV. A HY04					