

NOTES1:

UL Standard

- 1.Rated voltage/current : 150V / 8A
- 2.Withstanding voltage : AC1250V/1Min.

IEC Standard

1.	Pollution degree	2
	Overvoltage category	III
	Rate impulse voltage(KV)	2.5KV
	Rate voltage(V)	320V
	Rate current(A)	10A

NOTES2:

- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.5mm, Poles : N=04~48P(Total)
- 3.Operating temperature:-40°C~+105°C
- 4.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm							
TO	Over	Over	TO	Over	Over	Over	Over	0.1/10	
6	6 TO 10	10 TO 24	30	30 TO 60	60 TO 100	100 TO 150	150		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°	

5.RoHS Compliance

Ordering Information

JL15EDGRHB - 350 XX X XX






Pitch 350=3.5PH

No.of pins 2*2P~2*24P
04=2*2P
06=2*3P
08=2*4P
...

Housing Color B=Black (Convention)
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Serial code 01-99

2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66+GF	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES



Recommended P.C.B Layout(Top Side)

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		21.12.15

DRAW	SP.ZHENG	SCALE	FIT	JILN ® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONICS CO.,LTD	
		UNIT	mm		
		SHEET	A4	PART NO.	JL15EDGRHB-350XXXXX
		PROJ.	1/1	TITLE:	JL15EDGRHB-THR-3.5-2*XXP 插拔式公座/弯针
CHECK	W.CHEN				
APPROVE	J.CHEN				