

RoHS Compliant




说明:

1. 特性:

额定电压 :250V AC最大值
额定电流 :最大3A
接触阻抗 :30mΩ MAX.
绝缘阻抗 :3000MΩ MIN. at 500V DC
耐电压值 :250V AC RMS for 1Minute
工作温度 : -45℃~+85℃

2. 材料:

胶 芯 : PBT rated
端 子 : 铜合金
外 壳 : 铁合金/铜合金/不锈钢
前壳镀镍后壳镀锡/钝化



MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT	(QP)							
TANGENCY POINT	(TP)							
INTERSECTION POINT	(IP)							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE: DB15 母传统光孔		
X.	±0.25	CHECKED		DATE				
X.x	±0.20	APPROVED		DATE				
X.xx	±0.15	PART NO: LCK-201A15FC3A00A2						
ANGULAR	±3°	DRAWING NO:				REV: 04	SCALE: 1:1	UNIT: mm
						SIZE: A4	SHEET: 1/1	