

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		21.06.08

NOTES1:

UL Standard

- 1.Rated voltage/current : 300V / 8A
- 2.Withstanding voltage : AC1600V/1Min.
- 3.Wire range : 24~16AWG

IEC Standard

1.	Pollution degree	2	2	3
	Overvoltage category	II	III	III
	Rate impulse voltage(KV)	2.5KV	2.5KV	2.5KV
	Rate voltage(V)	320V	160V	160V
	Rate current(A)	8A		

- 2.Wire range : 0.2~1.0mm²,1.5mm²(sol)

NOTES2:





- 1.Dimension shall be interpreted per ASME Y14.5-2009
- 2.Pitch : 3.81mm, Poles : N=04~48P
- 3.Stripping length : 8~9mm
- 4.Operating temperature:-40°C~+105°C
- 5.Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						
To	Over	To	Over	To	Over	To	Over	0.1/10
6	10	10	24	30	60	100	150	0.1/10
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°

6.RoHS Compliance

Ordering Information

JL15EDGKNHCM-381	XX	X	XX	
Pitch 381=3.81PH	No.of pins 02=4P 03=6P 24=48P	Housing Color B=Black G=Green U=Blue R=Red W=White Y=Yellow O=Orange E=Grey	Serial code	



DRAW	SHUANGPING ZHENG	SCALE	FIT	 JILN® 东莞市锦凌电子有限公司 DONGGUAN JINLING ELECTRONIC CO.,LTD	
CHECK	LICHAO LIU	UNIT	mm		
APPROVE	YONGLIANG GAO	SIZE	A4	PART NO.	JL15EDGKNHCM-381XXXXX
		SHEET	1/1	TITLE:	JL15EDGKNHCM-3.81-2*XXP插拔式母座
		PROJ.			