



RoHS Compliant


A



SECTION:A-A




SECTION:B-B



USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME
A1	GND
A2	SSTXp1
A3	SSTXn1
A4	Vbus
A5	CC1
A6	Dp1
A7	Dn1
A8	SBU1
A9	Vbus
A10	SSRXn2
A11	SSRXp2
A12	GND

PIN NUMBER	SIGNAL NAME
B12	GND
B11	SSRXp1
B10	SSRXn1
B9	Vbus
B8	SBU2
B7	Dn2
B6	Dp2
B5	CC2
B4	Vbus
B3	SSTXn2
B2	SSTXp2
B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.8±0.10MM;DEFAULT TOLERANCE:±0.05

QUADRANT POINT TANGENCY POINT INTERSECTION POINT	QP TP IP		联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy
X. ± 0.25		DATE	2014.12.24
X.x ± 0.20		CHECKED	DATE
X.xx ± 0.15		APPROVED	DATE
ANGULAR $\pm 3^\circ$		PART NO:	LCK-TCM003-L90YL-G3
		REV:	04
		SCALE:	1:1
		UNIT:	mm
		DRAWING NO:	
		SIZE:	A4
		SHEET:	1/1