



RoHS Compliant



NOTES:

- Materials and electroplating specifications:
 - shell : stainless steel; Plating nickel 50 u";
 - terminal: High conductivity copper; Plating nickel 50 u", Solder foot gold plated 0.5u", Gold-plated 1u" in contact area.
 - Insulator: LCP UL94V-0 Color: Black
- SPECIFICATION:
 - CURRENT RATING: 5A MAX;
 - VOLTAGE: 100 VAC;
 - TEMPERATURE RANGE: -30 °C ~ +85 °C;
 - CONTACT RESISTANCE: 40 MILLIONHM MAX;
 - INSULATION RESISTANCE: 100 MEGOHMS MIN.
 - INSERTION FORCE : 5N~20N
 - UNMATING FORCE: 8N~20N
 - DURABILITY: 10,000 CYCLES UNMATING FORCE: 6N~20N CONTACT RESISTANCE: 50 MILLIONHM MAX;
 - Salt Spray: 24H



QUADRANT POINT TANGENCY POINT INTERSECTION POINT UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd							
		DESIGN	Andy	DATE	2014.12.24	TITLE:		
		CHECKED		DATE		TYPE C 16PIN 母座板上型 7.35mm		
		APPROVED		DATE				
		PART NO: LCK-TCF826-L735YL-G1			REV: 04	SCALE: 1:1	UNIT: mm	
		DRAWING NO:			SIZE: A4	SHEET: 1/1		