

说明:

1. 特性:

额定电压 :250V AC最大值

额定电流 :最大3A

接触阻抗 :30mΩ MAX.

绝缘阻抗 :3000MΩ MIN. at 500V DC

耐电压值 :250V AC RMS for 1Minute

工作温度 : -45℃~+85℃


2. 材料:

胶 芯 : PBT rated

端 子 : 铜合金

外 壳 : 铁合金/铜合金/不锈钢

前壳镀镍后壳镀锡/钝化



MEASURE POINT:

QUADRANT POINT

TANGENCY POINT

INTERSECTION POINT

QP

TP

IP

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:

X. ±0.25

X.x ±0.20

X.xx ±0.15

ANGULAR ±3°



联晟欣连接器 (深圳) 有限公司

Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24
CHECKED		DATE	
APPROVED		DATE	

PART NO: LCK-201A25MC3A00A2

DRAWING NO:

TITLE:

DB25 公传统光孔

REV: 04

SCALE: 1:1

UNIT: mm

SIZE: A4

SHEET: 1/1

