




RoHS Compliant



DC MATE PLUG



NOTES:

Rating: 0.5A 30V DC



Contact: Resistance 100mΩ Max.

Operating temperature: -20°C~70°C

Operating force: 3-20N

Operating Life: 5,000cycles

PIN	Item number	current
Ø1.0	LCK-DC-002-Z10	1A
Ø1.3	LCK-DC-002-Z13	1A
Ø1.65	LCK-DC-002-Z165	1A



6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
3	RESEALING	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
TR	PART NAME	1	QTY	MATER1AL

MEASURE POINT:

QUADRANT POINT

TANGENCY POINT

INTERSECTION POINT

UNLESS OTHERWISE

SPECIFIED, TOLERANCE:

X. ±0.25

X.x ±0.20

X.xx ±0.15

ANGULAR ±3°

QP

TP

IP



联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN

Andy

DATE

2014.12.24

TITLE:

PHONE JACKS

CHECKED

DATE

APPROVED

DATE

PART NO: LCK-DC-002-ZXXX

REV: 04

SCALE: 1:1

UNIT: mm

DRAWING NO:

SIZE: A4

SHEET: 1/1

