






MATING VIEW



MATING HEIGHT	4.0	4.5	5.0	5.5	6.0	6.5	7.0	7.5	8.0	8.5
MALE H1	0.95	1.95	0.95	1.0	1.95	1.95	2.0	2.95	4.0	
FEMALE H2	3.05	2.05	3.45	4.0	3.05	3.45	4.0	3.45	3.0	4.5




RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ±0.05

SER	REVISIONS	CHK	DATE

NOTES:







- HUOSINGT: HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- TERMINAL:PHOSPHOR BRONZE
PLATING:1μ" GOLD FLASH OVERALL 50~100μ" NICKEL UNDER PLATED.
- CODING INFORMATION: XDBM-08**-2*NP



PIN	Dimensions				PIN	Dimensions			
	A	B	C	C		A	B	C	C
8(2*4)	5.0	2.4	3.6	4.2	34(2*17)	15.4	12.8	14.0	14.6
10(2*5)	5.8	3.2	4.4	5.0	36(2*18)	16.2	13.6	14.8	15.4
12(2*6)	6.6	4.0	5.2	5.8	38(2*19)	17.0	14.4	15.6	16.2
14(2*7)	7.4	4.8	6.0	6.6	40(2*20)	17.8	15.2	16.4	17.0
16(2*8)	8.2	5.6	6.8	7.4	42(2*21)	18.6	16.0	17.2	17.8
18(2*9)	9.0	6.4	7.6	8.2	44(2*22)	19.4	16.8	18.0	18.6
20(2*10)	9.8	7.2	8.4	9.0	46(2*23)	20.2	17.6	18.8	19.4
22(2*11)	10.6	8.0	9.2	9.8	48(2*24)	21.0	18.4	19.6	20.2
24(2*12)	11.4	8.8	10.0	10.6	50(2*25)	21.8	19.2	20.4	21.0
26(2*13)	12.2	9.6	10.8	11.4	52(2*26)	22.6	20.0	21.2	21.8
28(2*14)	13.0	10.4	11.6	12.2	54(2*27)	23.4	20.8	22.0	22.6
30(2*15)	13.8	11.2	12.4	13.0	56(2*28)	24.2	21.6	22.8	23.4
32(2*16)	14.6	12.0	13.2	13.8	58(2*29)	25.0	22.4	23.6	24.2
34(2*17)	15.4	12.8	14.0	14.6	60(2*30)	25.8	23.2	24.4	25.0

CUSTOMER 深圳市连欣科技有限公司

REV: A	SIZE: A4	GENERAL TOLERANCE UNLESS OTHERWISE SPECIFIED X.X ±0.25 X.XX ±0.15 X.XXX ANG. 0°30'	PART NO: XDBM-08**-2*NP	
UNIT: mm	SCALE: 5:1		TITLE: 0.8 BOARD TO BOARD SMT V/T TYPE FEMALE	
SHEET NO: 1 OF 1				
			DRAWN BY: Kavin 2014-08-12	CHECKED BY:



RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ± 0.05

NOTES:

- 1.HUOSINGT: HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.TERMINAL:PHOSPHOR BRONZE
PLATING:1 μ "GOLD FLASHOVERALL 50~100 μ "NICKEL UNDER PLATED.

3.CODING INFORMATION: XDBF-08**-2*NP

PIN

STANDARD TYPE

MATING HEIGHT

40---4.0 height
45---4.5 height
50---5.0 height
55---5.5 height
60---6.0 height
65---6.5 height
70---7.0 height
75---7.5 height
80---8.0 height
85---8.5 height

0.8 SPACING

BOARD TO BOARD FEMALE WITH CUPULE TYPE
LIANXIN CONN BTB CONNECTOR SERIES

MATING HEIGHT	4.0	4.5	5.0	5.5	6.0	6.5	7.0	7.5	8.0	8.5
MALE H1	0.95	1.95	0.95	1.0	1.95	1.95	2.0	2.95	4.0	
FEMALE H2	3.05	2.05	3.45	4.0	3.05	3.45	4.0	3.45	3.0	3.5

PIN	Dimensions				PIN	Dimensions			
	A	B	C	C		A	B	C	C
8(2*4)	5.0	2.4	3.65	4.2	34(2*17)	15.4	12.8	#####	14.6
10(2*5)	5.8	3.2	4.45	5.0	36(2*18)	16.2	13.6	#####	15.4
12(2*6)	6.6	4.0	5.25	5.8	38(2*19)	17.0	14.4	#####	16.2
14(2*7)	7.4	4.8	6.05	6.6	40(2*20)	17.8	15.2	#####	17.0
16(2*8)	8.2	5.6	6.85	7.4	42(2*21)	18.6	16.0	#####	17.8
18(2*9)	9.0	6.4	7.65	8.2	44(2*22)	19.4	16.8	#####	18.6
20(2*10)	9.8	7.2	8.45	9.0	46(2*23)	20.2	17.6	#####	19.4
22(2*11)	10.6	8.0	9.25	9.8	48(2*24)	21.0	18.4	#####	20.2
24(2*12)	11.4	8.8	#####	10.6	50(2*25)	21.8	19.2	#####	21.0
26(2*13)	12.2	9.6	#####	11.4	52(2*26)	22.6	20.0	#####	21.8
28(2*14)	13.0	10.4	#####	12.2	54(2*27)	23.4	20.8	#####	22.6
30(2*15)	13.8	11.2	#####	13.0	56(2*28)	24.2	21.6	#####	23.4
32(2*16)	14.6	12.0	#####	13.8	58(2*29)	25.0	22.4	#####	24.2
34(2*17)	15.4	12.8	#####	14.6	60(2*30)	25.8	23.2	#####	25.0

CUSTOMER 深圳市连欣科技有限公司

REV: A	SIZE: A4	GENERAL TOLERANCE UNLESS OTHERWISE SPECIFIED X.X ± 0.25 X.XX ± 0.15 X.XXX ANG. 0°30'	PART NO: XDBF-08**-2*NP TITLE: 0.8 BOARD TO BOARD SMT V/T TYPE FEMALE
UNIT: mm	SCALE: 5:1		
SHEET NO: 1 OF 1			
DRAWN BY: <i>Kavin</i>	2014-08-12	CHECKED BY:	APPROVED BY:

SER	REVISIONS	CHK	DATE