

RoHS Compliant

NOTES:

Rating:DC 30V 5A





Contact:Resistance100mΩ Max.

Operating temperature: -20℃~70℃

Operating force: 3-20N

Operating Life: 5,000cycles

PIN	Item number
Ø2.0	LCK-DC-044A-Z200
Ø2.5	LCK-DC-044A-Z250



6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING1	C2680 T=0.3	MB: Cu Cu/Sn PLATE	
3	RERMDNAI	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
LTR	PART NAME	QTY	MATER1AL	

MEASURE POINT:

QUADRANT POINT

TANGENCY POINT

INTERSECTION POINT

UNLESS OTHERWISE

SPECIFIED,TOLERANCE:

X. ±0.25

X.x ±0.20

X.xx ±0.15

ANGULAR ±3°

QP

TP

IP



联晟欣连接器（深圳）有限公司

Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	PHONE JACKS
CHECKED		DATE			
APPROVED		DATE			
PART NO:	LCK-DC-044-ZXXX	REV:	04	SCALE:	1:1
DRAWING NO:		SIZE:	A4	SHEET:	1/1