

RoHS Compliant

NOTES:

Rating: 0.5A 30V DC


Contact: Resistance 100mΩ Max.

Operating temperature: -30°C~70°C

Operating force: 3-20N

Operating Life: 5,000cycles

PIN	Item number
Ø1.65	LCK-DC-005-Z165
Ø2.00	LCK-DC-005-Z200
Ø2.35	LCK-DC-005-Z235
Ø2.50	LCK-DC-005-Z250



6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
3	RERMDNAI	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
TR	PART NAME	1	QTY	MATER1AL

MEASURE POINT:

QUADRANT POINT

TANGENCY POINT

INTERSECTION POINT

UNLESS OTHERWISE

SPECIFIED, TOLERANCE:

X. ±0.25

X.x ±0.20

X.xx ±0.15

ANGULAR ±3°

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN
CHECKED
APPROVED

Andy
DATE
DATE

2014.12.24
DATE
DATE

TITLE:
PHONE JACKS

PART NO: LCK-DC-005-ZXXX

DRAWING NO:

REV: 04

SCALE: 1:1

SHEET: 1/1

UNIT: mm

UNIT: mm

UNIT: mm

DC MATE PLUG