







RoHS Compliant



- 一、Materials and electroplating specifications:
1.terminal: Brass; After nickel plating 30u",
tin plating 80u";
2.Insulator: Polyamide; Color:Black.
- 二、SPECIALITY:
1.RATED:30V Max/0.5A Max
2.CONTACT RESISTANCE: 100mΩ Max;
3.DIELECTRIC STRENGTH: 500V/AC 1min No Breakdown
4.INSULATION RESISTANCE:100MΩ Min. 500V DC
5.INSERTION FORCE:3.0Kgf Max
WITHDRAWAL FORCE:0.3Kgf Min
6.temperature:-20℃ to +70℃
7.Parts must comply with RoHS standards



P.C.B LAYOUT bottom view

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)	联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESIGN	Andy	DATE	2014.12.24
X. ±0.25	CHECKED		DATE	
X.x ±0.20	APPROVED		DATE	
X.xx ±0.15	PART NO: LCK-PJ-002		REV: 04	SCALE: 1:1
ANGULAR ±3°	DRAWING NO:		SIZE: A4	UNIT: mm
			SHEET: 1/1	