








RoHS Compliant



- 一、Materials and electroplating specifications:
- 1.terminal: Brass; After nickel plating 30u", tin plating 80u";
 2. Insulator: Polyamide; Color:Black.
- 二、SPECIALITY:
1. RATED:30V Max/0.5A Max
 2. CONTACT RESISTANCE: 100mΩ Max;
 3. DIELECTRIC STRENGTH: 500V/AC 1min No Breakdown
 4. INSULATION RESISTANCE:100MΩ Min. 500V DC
 5. INSERTION FORCE:3.0Kgf Max
WITHDRAWAL FORCE:0.3Kgf Min
 6. temperature:-20℃ to +70℃
 7. Parts must comply with RoHS standards



P.C.B LAYOUT bottom view

MEASURE POINT:			联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd					
QUADRANT POINT	QP							
TANGENCY POINT	TP							
INTERSECTION POINT	IP							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X.	±0.25	CHECKED		DATE		P J 插件式 4PIN 黑色主体 1.00mm		
X.x	±0.20	APPROVED		DATE		定位柱 插口 5.00mm尾端封装		
X.xx	±0.15	PART NO: LCK-PJ-003				REV: 04	SCALE: 1:1	
ANGULAR	±3°	DRAWING NO:				SIZE: A4	SHEET: 1/1	