






A

B

由 Autodesk 教育版产品制作



PCB开孔俯视图



## 产品要求:

1. 壳子:a. 不锈钢201 T:0.25mm  
b. 电镀镍
2. 端子:a. (C2680)/铜 T:0.18mm  
b. 电镀半金镍
3. 卡勾:a. 不锈钢201 T: 0.15mm

## 5. 塑胶: LCP

## 6. MECHANICAL:

INSERTION: 5~20N.

EXTRACTION: 8~20N.

DURABILITY: 5000 CYCLES

## 7. ELECTRICAL:

CURRENT: 3A MIN FOR VBUS;  
0.25A MIN FOR OTHER.

VOLTAGE: 5VAC MAX

WITHSTANDING VOLTAGE: 100V AC.

CONTACT RESISTANCE: 40mΩ MAX.

INSULATION RESISTANCE: 100MΩ MIN

## 8. ENVIRONMENTAL

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1		
A6	DPI	B7	DN2
A7	DNI	B6	DP2
		B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

深圳市连欣科技有限公司

APPROVED:	GENERAL TOLERANCES	TITLE:	Type-C 侧插长10.0母座 3A
	.X: ±0.30	PART NO:	XUBF-0314-0910
CHECKED:	.XX: ±0.15	DWG NO:	
	.XXX: ±0.005		
	ANGLE: ± 3.0°		
DRAWING:	SHEET: 1 OF 1	REV: A0	UNIT: mm
		SCALE: 1:1	SHEET: A4

G