

RoHS Compliant

NOTES:




Rating: 0.5A 30V DC

Contact: Resistance 100mΩ Max.

Operating temperature: -20°C~70°C



Operating force: 3-20N

Operating Life: 5,000cycles



DC MATE PLUG

PIN	Item number
Ø2.0	LCK-DC-012-Z200
Ø2.5	LCK-DC-012-Z250



6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS 11=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING1	C2680 T=0.3	MB: Cu Cu/Sn PLATE	
3	RERMDNAI	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
LTR	PART NAME	QTY	MATER1AL	

MEASURE POINT:

QUADRANT POINT

QP

TANGENCY POINT

TP

INTERSECTION POINT

IP

UNLESS OTHERWISE

SPECIFIED, TOLERANCE:

X. ±0.25

X.x ±0.20

X.xx ±0.15

ANGULAR ±3°



联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:
CHECKED		DATE		PHONE JACKS
APPROVED		DATE		
PART NO:	LCK-DC-012-ZXXX	REV:	04	SCALE: 1:1
DRAWING NO:		UNIT:	mm	SIZE: A4
		SHEET:	1/1	