

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 2018 BY TE CONNECTIVITY CORPORATION ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECO-18-011024	11JUL2018	DR	DR
	A2	ECO-18-017177	30OCT2018	DR	DR
	A4	REV PER ECN-22-188519	06DEC2022	SMR	PK
	A5	REV PER ECN-23-221248	14JUL2023	SMR	LM





1. MATERIAL: C11000 H02
2. PLATING: 0.0030-0.0050 SILVER PER ASTM B 700, TYPE 3, CLASS N, WITHOUT SUPPLEMENTARY CHROMATE TREATMENT BUT WITH A TARNISH RESISTANT TREATMENT, OVER 0.0010-0.0020 MATTE NICKEL
3. DIMENSION TO THEORETICAL SHARP CORNER

UNPLATED TAB CONTACT	A	1-2840393-1
TAB CONTACT	A	2840393-1
DESCRIPTION	REV	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.2
2 PLC	±0.10
3 PLC	±0.050
4 PLC	±
ANGLES	±2°

MATERIAL 1

FINISH 2

DWN D. RHEIN 16AUG2016
CHK D. RHEIN 24AUG2016
APVD D. RHEIN 24AUG2016
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT 18.0 g

TE Connectivity

NAME TAB CONTACT
HC-STAK 25 PLUG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2840393	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV A5