

A

B

C

D

E

F

修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12

1

2

3



4

5


6

7



8




LOCK CONFIGURATION (锁扣位置)



SECTION A-A



WITHOUT COVER




WITH COVER

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 125V, AC/DC.
4. 接触电阻: ≤20mΩ.
5. 绝缘电阻: ≥1000MΩ.
6. 额定电流: 1A , AC/DC.

CKT	DimA	DimB	DimC	DimD
2	1.25	3.25	7.50	7.50
3	2.50	4.50	8.75	8.75
4	3.75	5.75	10.00	10.00
5	5.00	7.00	11.25	11.25
6	6.25	8.25	12.50	12.50
7	7.50	9.50	13.75	13.75
8	8.75	10.75	15.00	15.00
9	10.00	12.00	16.25	16.25
10	11.25	13.25	17.50	17.50
11	12.50	14.50	18.75	18.75
12	13.75	15.75	20.00	20.00
13	15.00	17.00	21.25	21.25
14	16.25	18.25	22.50	22.50
15	17.50	19.50	23.75	23.75
16	18.75	20.75	25.00	25.00
17	20.00	22.00	26.25	26.25
18	21.25	23.25	27.50	27.50
19	22.50	24.50	28.75	28.75
20	23.75	25.75	30.00	30.00

适用线路板



A

B

C

D

E


F



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE:
产品名称: MX1.25针座立贴

X.X ±0.30 X.X* ±3°

APPD:
核准:PART NO:
产品编号: HDGC1251WV-S-nP

X.XX ±0.20 X.XX* ±2°

CHECK:
校对:

王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX* ±1°

DRAW:
绘图:

黄艳兰

2016-03-12 1:1 mm A001