

SPECIFICATIONS

Mechanical

Contact Retention Force: 0.10kg min.

Durability : 60 Cycles

Electrical

Voltage Rating: 25V

Current Rating: 0.5A

Contact Resistance: 50mΩ max.

Dielectric Withstanding Voltage: 250V AC/1 min.

Insulation Resistance: 100MΩ

Physical

Housing: Thermoplastic, UL 94V-0 rated in Black Color

Contact: Copper alloy

Plating: See "ORDERING INFORMATION"

Metal Spring: Copper alloy

Operating Temperature: -55℃ to +85℃

DDRIV SO DIMM Socket

AS Series


4.0mm Height SMT Type

0.50mm Pitch

260 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: A S A A8 2 * - H 4 * B 5 - * H

MEMORY MODULE SOCKET

HORIZONTAL TYPE

SINGLE ROW

NO. OF POS.
A8 = 260 POS.

SMT TYPE

CONTACT AREA PLATING
J= GOLD FLASH
Y= 50" GOLD PLATING
6= 100" GOLD PLATING
7= 150" GOLD PLATING
3= 300" GOLD PLATING

H=HALOGEN FREE
&LEAD FREE

7=TAPE REEL

4=PACKING TRAY

5=METAL LATCH

B=BLACK COLOR

R=REVERSE TYPE

S=STANDARD TYPE

4=4.0mm HEIGHT

DDR SODIMM

ASAA82*-H4SB5-*H	35.50	28.50
ASAA82*-H4RB5-*H	28.50	35.50
P/N	DIM. A	DIM. B