






- NOTE/注释:
1. SPECIFICATION/规格:
- 1.1 Rated current (额定电流) : 10.0 A For Vbus pin
1.25A For Vconn pin
0.25A For Other pin
 - 1.2 Voltage rating (额定电压) : 5V DC/AC; 20VMAX.
 - 1.3 Contact Resistance (接触阻抗) : 40 m Ω Max.
 - 1.4 Insulation Resistance (绝缘阻抗) :100MΩ Min.
 - 1.5 Withstanding voltage (耐电压) : 100 VAC/minute
 - 1.6 Mating force (插入力) : 5~20N .
 - 1.7 Unmating force (拔出力) : 8~20N.
 - 1.8 Durability Cycle(寿命循环):10,000 cycle
 - 1.9 Operating temperature (工作温度) : -55°~+85°







PIN ASSIGNMENT

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	Vbus	CC1	D+	D-	SBU1	Vbus	RX2-	RX2+	GND
GND	RX1+	RX1-	Vbus	SBUS2	D-	D+	CC2	Vbus	TX2-	TX2+	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TOLERANCE		NAME(INTENDED USE)		 广东富盈兴业有限公司 Guangdong Furuno Precision Electronic Technology Co.,LTD.	
		CUSTOMER DRAWING			
X.X ±0.30 X.' ±10'		PART NO.			
.XX ±0.20 .X' ± 8'		FY23-19TC242F2180-B181			
.XXX ±0.10 .XX' ± 5'					
UNITS mm		DESIGN: ZXM		TITLE: CF 24P母座沉板USB4.0 40G	
MATERILA -----		CHED:		DRAWG NO. FY23-19TC242F2180-B181	
FINISH -----		APPD:			
				SCALE 1:1	SHEET 1/2
					REV. A

FURUNO 广东富盈兴业有限公司
Guangdong FURUNO Precision Electronic Technology Co.,LTD.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



CONNECTOR (PCS)	REEL	CARTON
1500	1500	15000

TOLERANCE		NAME(INTENDED USE)		TITLE:	
X.X	±0.30 X.° ±10°	CUSTOMER DRAWING		FY23-19TC242F2180-B181	
.XX	±0.20 .X.° ± 8°	PART NO.		CF 24P母座沉板USB4.0 40G	
.XXX	±0.10 .XX° ± 5°	DESIGN: ZXM		DRAWG NO. FY23-19TC242F2180-B18	
UNITS	mm	CHED:		SCALE	
MATERILA	----	APPD:		SHEET	
FINISH	-----			REV.	
				1:1	
				A	