





REV.	REVISION DESCRIPTION	DATE


- NOTES:
1. Rated voltage: 250V AC.DC
 2. Rated current: 3A AC DC MAX
 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 4. Insulation resistance: $\geq 500 \text{ M}\Omega$
 5. Withstand voltage: 1100V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : PA66 UL94V-0(2)
 8. Pin Materials :Brass / Tin-Plated.
 9. Mates with QAC-Y Series Housing.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	QAC-2AS	2.50	7.90	9	QAC-9AS	20.00	25.40
3	QAC-3AS	5.00	10.40	10	QAC-10AS	22.50	27.90
4	QAC-4AS	7.50	12.90	11	QAC-11AS	25.00	30.40
5	QAC-5AS	10.00	15.40	12	QAC-12AS	27.50	32.90
6	QAC-6AS	12.50	17.90	13	QAC-13AS	30.00	35.40
7	QAC-7AS	15.00	20.40	14	QAC-14AS	32.50	37.90
8	QAC-8AS	17.50	22.90	15	QAC-15AS	35.00	40.40

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: QAC-AS	TITLE: 2.50 mm Pitch Wire To Board DIP Wafer
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:25/03/25
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DATE:25/03/25	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE:25/03/25	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV.: A



REV.	REVISION DESCRIPTION	DATE




NOTES:


1. Rated voltage: 250V AC.DC
2. Rated current: 3A AC DC MAX
3. Contact resistance: ≤20 mΩ
4. Insulation resistance: ≥500 MΩ
5. Withstand voltage: 1100V AC/minute
6. Ambient temprature: -40℃~+105℃
7. Material : PA66 UL94V-0(2)
8. Pin Materials :Brass / Tin-Plated.
9. Mates with QAC-Y Series Housing.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	QAC-2AWS	2.50	7.90	9	QAC-9AWS	20.00	25.40
3	QAC-3AWS	5.00	10.40	10	QAC-10AWS	22.50	27.90
4	QAC-4AWS	7.50	12.90	11	QAC-11AWS	25.00	30.40
5	QAC-5AWS	10.00	15.40	12	QAC-12AWS	27.50	32.90
6	QAC-6AWS	12.50	17.90	13	QAC-13AWS	30.00	35.40
7	QAC-7AWS	15.00	20.40	14	QAC-14AWS	32.50	37.90
8	QAC-8AWS	17.50	22.90	15	QAC-15AWS	35.00	40.40

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: QAC-AWS	TITLE: 2.50 mm Pitch Wire To Board DIP Wafer
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/03/25
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:25/03/25	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE:25/03/25	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV.: A




REV.	REVISION DESCRIPTION	DATE




- NOTES:
1. Rated voltage: 250V AC.DC
 2. Rated current: 3A AC DC MAX
 3. Contact resistance: ≤20 mΩ
 4. Insulation resistance: ≥500 MΩ
 5. Withstand voltage: 1100V AC/minute
 6. Ambient temprature: -40℃~+105℃
 7. Material : PA66 UL94V-0(2)
 8. Pin Materials :Brass / Tin-Plated.
 9. Mates with QAC-Y Series Housing.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	QAC-2AWD	2.50	7.90	9	QAC-9AWD	20.00	25.40
3	QAC-3AWD	5.00	10.40	10	QAC-10AWD	22.50	27.90
4	QAC-4AWD	7.50	12.90	11	QAC-11AWD	25.00	30.40
5	QAC-5AWD	10.00	15.40	12	QAC-12AWD	27.50	32.90
6	QAC-6AWD	12.50	17.90	13	QAC-13AWD	30.00	35.40
7	QAC-7AWD	15.00	20.40	14	QAC-14AWD	32.50	37.90
8	QAC-8AWD	17.50	22.90	15	QAC-15AWD	35.00	40.40

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: QAC-AWD	TITLE: 2.50 mm Pitch Wire To Board DIP Wafer
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/03/25
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:25/03/25	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE:25/03/25	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV.: A







- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 3A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 500\text{ M}\Omega$
 - 5. Withstand voltage: 1100V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0(2)
 - 8. Matched RoHS criteria
 - 9. Match with QAC-Y series housing
 - 10. Accepts QAC-RT Crimp Terminal.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	QAC-2R	2.50	8.20	9	QAC-9R	20.00	25.70
3	QAC-3R	5.00	10.70	10	QAC-10R	22.50	28.20
4	QAC-4R	7.50	13.20	11	QAC-11R	25.00	30.70
5	QAC-5R	10.00	15.70	12	QAC-12R	27.50	33.20
6	QAC-6R	12.50	18.20	13	QAC-13R	30.00	35.70
7	QAC-7R	15.00	20.70	14	QAC-14R	32.50	38.20
8	QAC-8R	17.50	23.20	15	QAC-15R	35.00	40.70

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: QAC-R		TITLE: 2.50 mm Pitch Housing	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 25/03/25	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 25/03/25	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 25/03/25	UNITS: mm	REV.: A
DRAWING NO:					







REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:

Rated voltage: 250V AC.DC
Rated current: 3A AC DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥500 MΩ
Withstand voltage: 1100V AC/minute
Ambient temperature: -40℃~+105℃
Wire range: AWG#26~#20
Materials:
Terminal: Phosphor bronze,Tin plated
Used in QAC-Y Series Housing.
Qty/Reel:6,000 PCS

Product name	Dimension mm				适用线规AWG
	A1	B1	A2	B2	
QAC-T-G	2.4	2.4	2.0	1.7	#22-20
QAC-T	2.2	2.4	1.8	1.5	#26-22

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: QAC-T		TITLE: 2.00 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/03/26	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu hui	DATE:25/03/26	SCALE: N/A	PAGE: 1/1
FINISH: 		APPD:Ren An De	DATE:25/03/26	UNITS: mm	REV.: A
DRAWING NO:					



NOTES:

Rated voltage: 250V AC/DC
Rated current: 3A AC/DC
Contact resistance: $\leq 20 \text{ m}\Omega$
Insulation resistance: $\geq 500 \text{ M}\Omega$
Withstand voltage: 1100V AC/minute
Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Wire range: AWG#26~#20
Materials:
Terminal: Phosphor bronze, Tin plated
Used in QAC-R Series Housing.
Qty/Reel: 7,000 PCS

Product name	Dimension mm				适用线规AWG
	A1	B1	A2	B2	
QAC-RT-G	2.4	2.4	2.0	1.7	#22-20
QAC-RT	2.1	2.5	1.7	1.6	#26-22

SECTION A-A

SECTION B-B

SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: QAC-RT		TITLE: 2.00 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 25/03/26	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu hui	DATE: 25/03/26	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 25/03/26	UNITS: mm	REV.: A