






REV.	REVISION DESCRIPTION	DATE	APPD


- NOTES:
1. Rated voltage: 50V AC.DC
 2. Rated current: 1A AC DC
 3. Contact resistance: $\leq 30\text{ m}\Omega$
 4. Insulation resistance: $\geq 100\text{ M}\Omega$
 5. Withstand voltage: 500V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
 7. Material : LCP UL94V-0




3	③	底座	LCP	1	UL94-V0
2	②	焊片	黄铜	2	镀锡
1	①	接触件	磷青铜	N	镀锡
序号	图号	名称	材料	数量	附件

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	NSH-2AB	2.0	5.2	10	NSH-10AB	9.0	12.2
3	NSH-3AB	2.0	5.2	11	NSH-11AB	10.0	13.2
4	NSH-4AB	3.0	6.2	12	NSH-12AB	11.0	14.2
5	NSH-5AB	4.0	7.2	13	NSH-13AB	12.0	15.2
6	NSH-6AB	5.0	8.2	14	NSH-14AB	13.0	16.2
7	NSH-7AB	6.0	9.2	15	NSH-15AB	14.0	17.2
8	NSH-8AB	7.0	10.2	-	-	-	-
9	NSH-9AB	8.0	11.2	-	-	-	-

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD					
.X: ± 0.25		X° : ± 3.0°		PRODUCT NAME:		TITLE:	
.XX: ± 0.15		.X° : ± 2.0°		DL10014 (NSH)-AB		1.0 mm Pitch Housing	
.XXX: ± 0.01		.XX° : ± 1.0°		DR: Chen Quan Long		DATE:24/12/05	
FINISH:				CHKD: Wu Hui		DATE:24/12/05	
DRAWING NO:		APPD:Ren An De		DATE:24/12/05		SCALE: N/A	
						PAGE: 1/1	
						UNITS: mm	
						REV. : A	



REV.	REVISION DESCRIPTION	DATE	APPD




- NOTES:
- 1. Rated voltage: 50V AC/DC
 - 2. Rated current: 1A AC/DC
 - 3. Contact resistance: $\leq 30\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 100\text{ M}\Omega$
 - 5. Withstand voltage: 500V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material: LCP UL94V-0


3	③	底座	LCP	1	UL94-V0
2	②	焊片	黄铜	2	镀锡
1	①	接触件	磷青铜	N	镀锡
序号	图号	名称	材料	数量	附件

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	NSH-2AWB	2.0	5.2	10	NSH-10AWB	9.0	12.2
3	NSH-3AWB	2.0	5.2	11	NSH-11AWB	10.0	13.2
4	NSH-4AWB	3.0	6.2	12	NSH-12AWB	11.0	14.2
5	NSH-5AWB	4.0	7.2	13	NSH-13AWB	12.0	15.2
6	NSH-6AWB	5.0	8.2	14	NSH-14AWB	13.0	16.2
7	NSH-7AWB	6.0	9.2	15	NSH-15AWB	14.0	17.2
8	NSH-8AWB	7.0	10.2	-	-	-	-
9	NSH-9AWB	8.0	11.2	-	-	-	-

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL10014 (NSH)-AWB		TITLE: 1.0 mm Pitch Housing	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 24/12/05	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 24/12/05	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 24/12/05	UNITS: mm	REV.: A
DRAWING NO:					



NOTES:
Rated voltage: 50V AC/DC
Rated current: 1A AC/DC
Contact resistance: $\leq 30 \text{ m}\Omega$
Insulation resistance: $\geq 100 \text{ M}\Omega$
Withstand voltage: 500V AC/minute
Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Wire range: AWG#32~#28
Materials:
Terminal: Phosphor bronze, Tin plated



GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME:		TITLE:			
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DL10014 (NSH)-T		1.0 mm Pitch Wire To Board Crimp Terminal			
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE 18/05/02	PART NO:			
FINISH:		CHKD: Wu Hui	DATE 18/05/02	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE 18/05/02	UNITS: mm		REV.: A	