






RoHS

REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	更新尺寸			2025.08.22

SPECIFICATIONS
Current Rating: 50 Amps @ 500V AC
Temperature Rating: -40 °C to 125 °C
Insulator: PBT , UL 94V-0
Contacts: Brass,
Finish: Tin plated over Nickel
Fuse Size: Maxi automotive blade Fuses



3D VIEW



Ø4.20 DIA(4) PLS

适用线路板(PCB LAYOUT)

X.±0.50	X.°±	PART NO: XF-507P-A		XFCN 兴飞连接器	
.X±0.25	.X°±				
.XX±0.15	.XX°±	TITLE: 超大型刀片汽车保险丝座		0769-82001899	
.XXX±0.10	.XXX°±			www.xfconn.com	
UNITS:	mm			DWG NO: /	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang		
		CHKD	Liu Wei	VIEW	
		DRAW	Chen HongJiang	SCALE	SHEET
		DATE	2025.08.22	NONE	REV
					1/1 A1