








SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Soldering Temperature:260°C±5° 5S

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	6.00	3.20	4.80	9.20
Alternate				

Ordering Information

PZ 254 - * - N - S - * - ** - R - *

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
2-40Pin

Type
2P (2Pin)
3P (3Pin)
4P (4Pin)

Length
(产品规格)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Packing
R=Reel
+Cap
(编带+盖)

1=TYPE 1
2=TYPE 2

			GENERAL TOLERANCE		制 图		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审 核	CHECK				
			X.X	±0.30	批 准	APPROVAL	产品名称	2.54单排 排针 贴片	版 本	A
			X.XX	±0.20	比 例	SCALE	产品料号	(塑高2.5) 编带+盖	REV.	
			X.XXX	±0.10	投 影	Projection	PART NO.	PZ254-1-N-S-2.5-XX-R-X (L9.2)	单 位	mm
序号	变更内容	日期	Angle	±3.0°	材料	MATERIAL	页 次		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE					SHEET			